



s.30 DZR

12 - 54 mm compression ends for insulation dezincification-resistant

Several governmental authorities recommend use of special alloys for valves handling water in areas where there is a problem of dezincification.

RUB DZR valves are designed to meet such requirements. Through the use of new technology these valves retain the reliability and competitiveness of brass, but are comparable to bronze in corrosion resistance.

Be kind with yourself, make sure the valve that brings you pure fresh water is an *RuB* DZR valve.











OUALITY

- · 24h 100% seal test guaranteed
- Dual sealing system allows valve to be operated in either direction making installation easier
- · No metal-to-metal moving parts
- · No maintenance ever required
- · Handle clearly shows ball position
- · Silicone-free lubricant on all seals
- · Handle stops on body to avoid stress at stem
- · Chrome plated DZR brass ball for longer life

BODY

- Hot forged sand blasted DZR unplated body and cap sealed with Loctite® or equivalent thread sealant
- Dezincification resistant ADZ-T and ADZ-P brass approved to SBN-PFS 1983:2 and NR-BFS 1988:18 specifications
- Extended stem forged in one piece with body allows perfect sealing and easy operation when valve is isolated

STEM

- Maintenance-free, double FPM O-rings at the stem for maximum safety
- · Unplated DZR brass stem

SEALING

- Pure PTFE self-lubricating seats with flexible-lip design

CONNECTIONS

· Compression ends to EN 1254-2 and NKB no.12

FLOW

Full port to DIN 3357 for maximum flow

HANDLE

- Geomet® carbon steel handle with thick PVC dip coating. Handle coating offers both thermal and electrical protection
- · Handle removable with valve in service
- · WARNING: do not exceed reasonable temperature and/or electrical load

WORKING PRESSURE & TEMPERATURE

- 16 bar (230 PSI) non-shock cold working pressure
- -20°C to +120°C (-4°F to +250°F)
- WARNING: freezing of the fluid in the installation may severely damage the valve

UPON REQUEST

- · Stainless steel ball (1.4401 / AISI 316)
- · Glass filled PTFE seals
- · Custom design

PED DIRECTIVE

 The product described in this document meets the requirements of the PED Directive 2014/68/UE and according to art.4 par.3, it does not require CE marking; it cannot be used with dangerous gases in sizes larger than 25 mm

APPROVED BY OR IN COMPLIANCE WITH

- RoHS Compliant (EU)
- EAC Declaration of conformity (Russia, Kazakhstan, Belarus)
- Kiwa-Swedcert (Sweden)
- · Ri.se. / Boverket (Sweden)

NOTE: approvals apply to specific configurations/sizes only.

OPTIONS

- Oval lockable handle
- Patented locking device 2
- Stainless steel handle (1.4016 / AISI 430)
- T-handle
- · RuB memory stop designed to be installed with our stubby handle
- Short stem design
- · Stubby handle




s.30 DZR XCES30 - 5813

Each user should perform his own tests to find out the suitability for his particular application. BONOMI INDUSTRIES makes no warranty, express or implied, as to the shape, fit or function of a product for any application. Contact us or consult with your supplier for additional information on the suitability of the BONOMI INDUSTRIES products with your specific field of use.



	Part description	Q.ty	Material
1	Unplated body	1	CW602N
2	Ball seat	2	PTFE
3	Chrome plated ball	1	CW602N
4	Unplated end-cap	1	CW602N
5	Olive	2	CW603N - CW508L - CW602N
6	Unplated nut	2	CW617N
7	Unplated extended stem O-ring design	1	CW602N
8	O-Ring	2	FPM
9	Unplated nut	1	CW617N
10	Geomet® nut	1	C4C (EN10263-2)
11	White PVC coated Geomet® steel handle	1	DD11 (EN10111)




Hollow ball for D 35-42-54

Code	S30C12	S30D15	S30D18	S30E22	S30F28	S30G35	S30H42	S30I54
D (mm)	12	15	18	22	28	35	42	54
DN (mm)	10	15R	15R	20R	25R	32R	40R	50R
L (mm)	67	72	78.5	79	90.5	110	128.5	142
A (mm)	100	100	100	120	120	158	158	158
H (mm)	85	88	88	95	99	124	130	137
CH (mm)	19	24	27	32	38.5	48	54	70
Kv (m³/h)	8.2	28	28	42	70	80	125	179

DN shows the nominal flow diameter. Actual flow diameter complies with full port DIN 3357 part 4.

PRESSURE-TEMPERATURE CHART



PRESSURE DROP CHART

