



# s.90 ACS M/M

Male/Male 1/4" - 2" ISO 228











# **OUALITY**

- · 24h 100% seal test guaranteed
- Dual sealing system allows valve to be operated in either direction making installation easier
- · No metal-to-metal moving parts
- · No maintenance ever required
- · Handle clearly shows ball position
- · Silicone-free lubricant on all seals
- · Chrome plated brass ball for longer life
- · Handle stops on body to avoid stress at stem

#### **BODY**

- Hot forged sand blasted, external nickel plated brass body and cap sealed with Loctite® or equivalent thread sealant
- Finest brass according to EN 12165 and EN 12164 specifications

# **STEM**

- Blowout-proof nickel plated brass stem
- · Maintenance-free, two O-rings at the stem (EPDM + FPM) for maximum safety

#### **SEALING**

- Pure PTFE self-lubricating seats with flexible-lip design

#### **THREADS**

· ISO 228 parallel male by male threads

#### **FLOW**

· Full port to DIN 3357 for maximum flow

#### HANDLE

- Geomet® carbon steel handle with thick PVC dip coating. Handle coating offers both thermal and electrical protection
- · Handle removable with valve in service

#### **WORKING PRESSURE & TEMPERATURE**

- 40 bar (600 PSI) non-shock cold working pressure
- -40°C to +180°C (-40°F to +356°F)
- WARNING: freezing of the fluid in the installation may severely damage the valve

#### **UPON REQUEST**

- Stainless steel ball (1.4401 / AISI 316)
- · Glass filled PTFE seals
- · Custom design

# **PED DIRECTIVE**

- According to 2014/68/UE module A: it cannot be used with dangerous gases in sizes larger than 25mm

#### APPROVED BY OR IN COMPLIANCE WITH

- $\cdot \ \ \text{Water Regulations Advisory Scheme (United Kingdom)}$
- EAC Declaration of conformity (Russia, Kazakhstan, Belarus)
- RoHS Compliant (EU)
- · Attestation de Conformité Sanitaire (France)

**NOTE:** approvals apply to specific configurations/sizes only.

#### **OPTIONS**

- Oval lockable handle
- Patented locking device
- Stainless steel handle (1.4016 / AISI 430) 3
- T-handle 4
- · Stem extension
- $\cdot$  RuB memory stop is designed to be installed with our stubby handle
- Dezincification resistant brass body and components
- · Stubby handle





# **s.90 ACS MM** XCES9099MM - 0

Each user should perform his own tests to find out the suitability for his particular application. BONOMI INDUSTRIES makes no warranty, express or implied, as to the shape, fit or function of a product for any application. Contact us or consult with your supplier for additional information on the suitability of the BONOMI INDUSTRIES products with your specific field of use.



	Part description	Q.ty	Material
1	Nickel plated body (external nickel plated, unplated inside)	1	CW617N
2	Seat	2	PTFE
3	Chrome plated ball	1	CW617N
4	Nickel plated end-cap (external nickel plated, unplated inside)	1	CW617N
5	Nickel plated stem O-ring design	1	CW617N
6	Geomet® nut	1	C4C (EN10263-2)
7	O-ring	1	EPDM
8	O-ring	1	FPM
9	Red PVC coated Geomet® steel handle	1	DD11 (EN10111)






1 1/4"-2" hollow ball

Code	S90B2299	S90C2299	S90D2299	S90E2299	S90F2299	S90G2299	S90H2299	S9012299
D (Size)	1/4"	3/8"	1/2"	3/4"	1"	1 1/4"	1 ½"	2"
DN (mm)	8	10	15	20	25	32	40	50
l (mm)	9	9	11	12	14	15	17	19
L (mm)	50.5	50.5	62	67	80	91.5	103	120
G (mm)	21	21	27	29	36	41	48	56
A (mm)	82	82	100	120	120	158	158	158
H (mm)	38	38	43	50	54	73	79	86
CH (mm)	15	18	22	27	35	44	54	68
Kv (m^3/h)	3,9	8,2	28	42	70	80	125	179

DN shows the nominal flow diameter. Actual flow diameter complies with full port DIN 3357 part 4. Ball valves are marked CE on handle from 1 1/4" to 2": CE XXCODEXX Cat I-A

### PRESSURE-TEMPERATURE CHART



# PRESSURE DROP CHART

